

# Watertight Case

## Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion-free
- Screen printing and resin label space



**IP67 RATING** **ATA 300** **MIL SPECS** DEF STAN 81-41  
STANAG 4280

## Specification

|                      |                    |
|----------------------|--------------------|
| External Dimensions  | 414 x 345 x 129 mm |
| Internal Dimensions  | 380 x 270 x 115 mm |
| Cover Depth - Bottom | 36 + 79 mm         |
| Weight               | 2.1 kg             |
| Temperature Range    | -30 ... 90 °C      |
| Capacity             | 11.8 l             |
| Protection Rating    | IP67               |

## Material Specification

|          |                         |
|----------|-------------------------|
| Base     | Polypropylene Copolymer |
| Latches  | Nylon                   |
| O-Ring   | Polymer                 |
| Moulding | Injection Moulded       |

## Accessories

Cubed & convulated foams, panels, shoulder strap

## Youtube Video



Art. Nr.  
RND 600-00275