

Watertight Case

Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Screen printing and resin label space



IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

Specification

External Dimensions	502 x 415 x 141 mm
Internal Dimensions	465 x 335 x 125 mm
Cover Depth - Bottom	40 + 85 mm
Weight	2.9 kg
Temperature Range	-30 ... 90 °C
Capacity	19.5 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Accessories

Cubed & convulated foams, lid organizer, panels, shoulder strap

Youtube Video



Art. Nr.
RND 600-00276