

Watertight Case

Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Screen printing and resin label space



Specification

IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

External Dimensions	687 x 528 x 286 mm
Internal Dimensions	620 x 460 x 250 mm
Cover Depth - Bottom	60 + 190 mm
Weight	9.6 kg
Temperature Range	-30 ... 90 °C
Capacity	71.3 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded
Trolley	Metal + Plastic
Wheels	With Stainless Steel Pin

Accessories

Cubed & convulated foams

Youtube Video



Art. Nr.
RND 600-00280