

Watertight Case with Padded Dividers



Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Screen printing and resin label space
- Padded dividers set with movable compartments to better organize and protect your instruments
- Convoluted foam in the lid



Specification

IP67 RATING **ATA 300** **MIL SPECS** DEF STAN 81-41
STANAG 4280

External Dimensions	336 x 300 x 148 mm
Internal Dimensions	300 x 225 x 132 mm
Cover Depth - Bottom	33 + 99 mm
Weight	2.44 kg
Temperature Range	-30 ... 90 °C
Capacity	8.91 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.
RND 600-00295