

# Watertight Case with Cubed Foam



## Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Screen printing and resin label space
- Convoluted foam in the lid and cubed foam in the bottom with pick and pluck system to easily adapt the case to your objects



## Specification

**IP67 RATING** **ATA 300** **MIL SPECS** DEF STAN 81-41  
STANAG 4280

External Dimensions	555 x 428 x 306 mm
Internal Dimensions	500 x 350 x 280 mm
Cover Depth - Bottom	58 + 222 mm
Weight	5.84 kg
Temperature Range	-30 ... 90 °C
Capacity	49 l
Protection Rating	IP67

## Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

**Art. Nr.**  
**RND 600-00310**