

Watertight Case with Padded Dividers, Organizer & Trolley



Features

- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Polyamide pins, corrosion free
- Screen printing and resin label space
- Padded dividers set with movable compartments to better organize and protect your instruments
- Lid organizer with zipl closures and document pouch
- Trolley and wheels for simplify the transport



Specification

IP67 RATING

MIL SPECS DEF STAN 81-41
STANAG 4280

External Dimensions	594 x 473 x 270 mm
Internal Dimensions	538 x 405 x 245 mm
Cover Depth - Bottom	50 + 195 mm
Weight	8.52 kg
Temperature Range	-30 ... 90 °C
Capacity	53.38 l
Protection Rating	IP67

Material Specification

Base	Polypropylene Copolymer
Latches	Polyamide
O-Ring	Polymer
Moulding	Injection Moulded

Art. Nr.
RND 600-00314