Reflective Marking Tape



Features

- Can be effectively used in any environment, and takes literally minutes to apply
- Coated with a permanent high visibility adhesive coat
- Allows for a long term bond, and with it not being water based, it will not break down under testing environmental conditions
- A paper backing liner is applied to protect the PSA (pressure sensitive adhesive) prior to application
- Suitable for marking out potentially hazardous or dangerous areas
- Suitable for outdoor use
- UV-resistant, Not Tested



Testing Method

Specification

Tape Colour	White	
Tape Length	10 m	
Tape Width	50 mm	
Material Thickness	0.128 mm (PET)	
Total Applied Thickness	0.24 mm	Caliper Method
Adhesive Material	Acrylic	
Adhesive Thickness	0.02 mm	
Overall Thickness	0.148 mm	
Peeling Strength	1 kg/inch	PSTC-1
Holding Power	72 HR	PSTC-7
Temperature range	-20 70 °C	

Art. Nr. RND 605-00031