

Wiping Paper Roll



Features

- Strong and absorbent ensuring you less waste and efficient drying
- High capacity roll
- Use for mopping up liquids and drying hands



Specifications

Typical Properties		Unit	Value	Test Methods
Basis Weight		g/ m ²	19	GB/T 26379
Colour		—	White	Corporation Standards
Bases	Wood Pulp	%	100	
Thickness		mm	0.08	GB/T 24218.2-2009
Dry Tensile Strength	MD	Gf/25mm	≥800	GB/T26379 GB/T 24218.3-2010
	CD	Gf/25mm	≥400	
Wet Tensile Strength	MD	Gf/25mm	≥250	
	CD	Gf/25mm	≥100	
Speed of Absorbability		S/5cm	≤ 10	Corporation Standards GB/ T 24218.6-2010
Absorptive Capacity		%	≥400	
Fluorescent Substance		—	-	YY0331-2002P
Whiteness		%	≥80	
Testing Temperature: 23°C		Testing Humidity: 60%		

Art Nr.	Size	Form
RND 605-00181	220 x 380 mm	500 sheets/Roll