

# Multifunctional Wiping Cloth



## Features

- Excellent overall performance across different industries and applications
- Ideal for cleaning as you go, catching spills and drips as well as cleaning work surfaces, sinks, utensils and machinery
- Exceptional food and dirt pick-up



## Specifications

Typical Properties		Unit	Value	Test Methods & Voluntary standards
Basis Weight		g/ m <sup>2</sup>	67±3	FZ/T60003-91 GB/T 26379
Colour		—	Blue 2#	Corporation Standards
Bases	Wood Pulp	%	55±2%	
	PET	%	45±2%	
Thickness		mm	0.28±5%	FZ/T60004-91 GB/T 24218.2-2009
Fracture Strength	MD	N/5cm	≥150	FZ/T60005-91 GB/T26379
	CD	N/5cm	≥70	
Fracture Elongation	MD	%	≤50	FZ/T60005-91 GB/T 24218.3-2010
	CD	%	≤100	
Speed of Absorbability		mm/30s	≥45	GB/T 24218.6-2010
Absorptive Capacity		%	≥450	
Fluorescent Substance		—	NO	YY0331-2002P
Surface Active Substances		%	-	
Residue on Ignition		%	-	
Testing Temperature: 23°C		Testing Humidity: 55%		

Art Nr.	Size	Form
RND 605-00184	230 x 340 mm	500 sheets/Roll