

Multifunctional Wiping Cloth



Features

- Excellent overall performance across different industries and applications
- Ideal for cleaning as you go, catching spills and drips as well as cleaning work surfaces, sinks, utensils and machinery
- Exceptional food and dirt pick-up



Specifications

Typical Properties		Unit	Value	Test Methods & Voluntary standards
Basis Weight		g/ m ²	55±3	FZ/T60003-91 GB/T 26379
Colour		—	White	Corporation Standards
Bases	Wood Pulp	%	55±2%	
	PET	%	45±2%	
Thickness		mm	0.28±5%	FZ/T60004-91 GB/T 24218.2-2009
Fracture Strength	MD	N/5cm	≥120	FZ/T60005-91 GB/T26379
	CD	N/5cm	≥30	
Fracture Elongation	MD	%	≤50	FZ/T60005-91 GB/T 24218.3-2010
	CD	%	≤150	
Speed of Absorbability)		mm/30s	≥45	GB/T 24218.6-2010
Absorptive Capacity)		%	≥500	
Fluorescent Substance)		—	NO	YY0331-2002P
Surface Active Substances)		%	-	
Residue on Ignition		%	-	
Testing Temperature: 23°C		Testing Humidity: 55%		

Art Nr.	Size	Form
RND 605-00185	300 x 300 mm	100 pcs/Bag