

# Microfiber Wiping Cloth



## Features

- Perfect on windows and surfaces that tend to streak
- Ideal for cleaning as you go, catching spills and drips as well as cleaning work surfaces, sinks, utensils and machinery
- Picks up dust, dirt, grease, and bacteria



## Specifications

Typical Properties		Unit	Value	Test Methods & Voluntary standards
Basis Weight		g/ m <sup>2</sup>	360±10	FZ/T60003-91 GB/T 26379
Colour		—	Blue	Corporation Standards
Bases	PET	%	80±2%	
	Nylon	%	20±2%	
Thickness		mm	0.28±5%	FZ/T60004-91 GB/T 24218.2-2009
Speed of Absorbability		mm/30s	≥45	GB/T 24218.6-2010
Absorptive Capacity		%	≥500	
Fluorescent Substance		—	-	
Surface Active Substances		%	-	
Residue on Ignition		%	-	
Testing Temperature: 23°C				Testing Humidity: 55%

Art Nr.	Size
RND 605-00186	400 x 400 mm