

# Dual Locking Miniature Spacers

## Pack of 50



### FEATURES:

Dual locking circuit board support (Pack of 50)

Top and bottom hole  $\varnothing$  2.54 mm  $\pm$ 0.05 mm

Panel thickness 1.63 mm

### SPECIFICATION:

Material PA 66, UL94-V2

Bore 2.54 mm

Colour Natural

### PRODUCT RANGE:

Art. Nr.	A	Length
RND 610-00041	1.6 mm	9 mm
RND 610-00042	3.2 mm	10.6 mm
RND 610-00043	4.8 mm	12.2 mm
RND 610-00044	6.4 mm	13.8 mm
RND 610-00045	7.9 mm	15.3 mm
RND 610-00046	9.5 mm	16.9 mm
RND 610-00047	11.1 mm	18.5 mm
RND 610-00048	12.7 mm	20.1 mm
RND 610-00049	14.3 mm	21.7 mm
RND 610-00050	15.9 mm	23.3 mm
RND 610-00051	22.2 mm	29.6 mm

