

# Hex Nuts

## Features

- No burrs and sharp edges
- Material: A2 stainless steel
- Passivated finish
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN 934 standard

Thread (6g)	PART NO.
M2x0.4	RND 610-00483
M2.5x0.45	RND 610-00484
M3x0.5	RND 610-00485
M4x0.7	RND 610-00486
M5x0.8	RND 610-00487
M6x1.0	RND 610-00488
M8x1.25	RND 610-00489

Thread(6H)	S	M	E (Min)
M1x0.25	2.40~2.50	0.55~0.80	2.71
M1.2x0.25	2.90~3.00	0.75~1.00	3.28
M1.4x0.3	2.90~3.00	0.95~1.20	3.28
M1.6x0.35	3.02~3.20	1.05~1.30	3.41
M2x0.4	3.82~4.00	1.35~1.60	4.32
M2.5x0.45	4.82~5.00	1.75~2.00	5.45
M3x0.5	5.32~5.50	2.15~2.40	6.01
M3.5x0.6	5.82~6.00	2.55~2.80	6.58
M4x0.7	6.78~7.00	2.90~3.20	7.66
M5x0.8	7.78~8.00	3.70~4.00	8.79

Thread(6H)	S	M	
M6x1.0	9.78~10.00	4.70~5.00	11.05
M8x1.25	12.73~13.00	6.14~6.50	14.38
M10x1.5	16.73~17.00	7.64~8.00	18.90
M12x1.75	18.67~19.00	9.64~10.00	21.10
M14x2.0	21.67~22.00	10.30~11.00	24.49
M16x2.0	23.67~24.00	12.30~13.00	26.75
M18x2.5	26.16~27.00	14.30~15.00	29.56
M20x2.5	29.16~30.00	14.90~16.00	32.95
M24x3.0	35.00~36.00	17.00~19.00	39.55
M30x3.5	45.00~46.00	22.70~24.00	50.85

