

# Flat Washer

## Features

- No burrs and sharp edges
- Material: SPCC carbon steel, 140 HV
- Finish: Trivalent blue zinc / 3.8  $\mu\text{m}$  min.
- Material and finish comply with 211/65/EU (RoHS)
- Meets DIN125A standard

M	PART NO.
M2	RND 610-00615
M2.5	RND 610-00633
M3	RND 610-00634
M4	RND 610-00635
M5	RND 610-00636
M6	RND 610-00637

M	DI	DO	T
M1.6	1.70~1.84	3.70~4.00	0.25~0.35
M2	2.20~2.34	4.70~5.00	0.25~0.35
M2.3	2.50~2.64	5.70~6.00	0.45~0.55
M2.5	2.70~2.84	5.70~6.00	0.45~0.55
M2.6	2.80~2.94	6.64~7.00	0.45~0.55
M3	3.20~3.38	6.64~7.00	0.45~0.55
M3.5	3.70~3.88	7.64~8.00	0.45~0.55
M4	4.30~4.48	8.64~9.00	0.70~0.90
M5	5.30~5.48	9.64~10.00	0.90~1.10
M6	6.40~6.62	11.57~12.00	1.40~1.80
M8	8.40~8.62	15.57~16.00	1.40~1.80

M	DI	DO	T
M10	10.50~10.77	19.48~20.00	1.80~2.20
M12	13.00~13.27	23.48~24.00	2.30~2.70
M14	15.00~15.27	27.48~28.00	2.30~2.70
M16	17.00~17.27	29.48~30.00	2.70~3.30
M18	19.00~19.33	33.48~34.00	2.70~3.30
M20	21.00~21.33	36.38~37.00	2.70~3.30
M22	23.00~23.33	38.38~39.00	2.70~3.30
M24	25.00~25.33	43.38~44.00	3.70~4.30
M26	27.00~27.33	49.38~50.00	3.70~4.30
M28	29.00~29.33	49.38~50.00	3.70~4.30
M30	31.00~31.39	55.28~56.00	3.70~4.30

