

# Flexible Inspection Camera Probe, 3.9 mm



## Features

- With bright, integrated LED lighting
- Universal micro camera with small camera head
- Ideal for hard-to-reach places thanks to the very small camera head
- Powerful object lighting thanks to 4 high-performance LEDs
- Diverse range of applications thanks to the 1 m long camera



## Specification

Probe Diameter	3.9 mm
Probe Length	1 m
Number of LEDs	6
LED Colour	White
Focus	10 ... 50 mm
Camera Resolution	320 x 240 Pixels
Operating Temperature	0 ... 45 °C
Field of View	80°
Light Output	500 +/- 100 Lux
Protection Rating	IP67 (Camera and Flexible Tube Only)

## Art. Nr.

**RND 715-00001**