

Semi-Rigid Inspection Camera Probe, 5.5 mm



Features

- With bright, integrated LED lighting
- Universal micro camera with small camera head
- Ideal for hard-to-reach places thanks to the very small camera head
- Powerful object lighting thanks to 6 high-performance LEDs
- Diverse range of applications thanks to the 1 m long camera



Specification

Probe Diameter	5.5 mm
Probe Length	1 m
Number of LEDs	6
LED Colour	White
Focus	30 ... 60 mm
Camera Resolution	640 x 480 Pixels
Operating Temperature	0 ... 45 °C
Field of View	60°
Light Output	520 +/- 100 Lux
Camera Resolution	IP67 (Camera and Flexible Tube Only)

Art. Nr.

RND 715-00002