



PIN ASSIGNMENT:

P1	_____	P2
1	_____	1
2	_____	2
3	_____	3
4	_____	4
5	_____	5
6	_____	6
7	_____	7
8	_____	8
9	_____	9
SHELL	_____	SHELL

Product Number	CU.P/NO	Length+/- (mm)	Packing
301-16-437	RND 765-00022	1800+/-10mm	1pc/poly bag with single color printed RND Connect logo++ RND Label
301-16-438	RND 765-00023	500+/-10mm	
301-16-439	RND 765-00024	3000+/-30mm	
301-16-440	RND 765-00025	5000+/-50mm	
301-16-441	RND 765-00026	10000+/-50mm	
301-16-442	RND 765-00027	15000+/-50mm	

NOTES:

ELECTRICAL CHARACTER:

- 1.100% OPEN&SHORTTESTING.
- 2.ROHS and REACH COMPLIANT.
3. Copper OD Toleranle +/- 0.02mm
- 4.connector connection method: soldering.
- 5.THIS PRODUCT INCLUDED THE RAW

MATERIAL:

PVC ~ COPPER WIRE ~ Gold-plated PBT ~ solder wire
 copper ~ nickel-plated copper
 ~ nickel plated Iron shell ~

Temperature Range: 10°C...60°C

C	CONNECTOR 2	DB 9P MALE NICKEL-PLATED	
B	CONNECTOR 1	DB 9P FEMALE NICKEL-PLATED	
A	CABLE	9C+1 28AWG(7X0.12BC) +D7X0.12BC +AL/MYLAR OD5.0MM color:BEIGE	
NO	ITEM	DESCRIPTION	