



PIN ASSIGNMENT:

CN 37P M		CN 37P F
1	—————	1
2	—————	2
3	—————	3
34	—————	34
35	—————	35
36	—————	36
37	—————	37
SHELL	—————	SHELL

NOTES:

ELECTRICAL CHARACTER:

- 1.100% OPEN&SHORTTESTING.
- 2.ROHS and REACH COMPLIANT.
3. Copper OD Toleranle +/- 0.02mm
- 4.connector connection method: soldering.
- 5.THIS PRODUCT INCLUDED THE RAW MATERIAL:

PVC ~ COPPER WIRE ~ Gold-plated ~ PBT ~ solder wire
 copper ~ nickel-plated copper
 ~ nickel plated Iron shell ~

Temperature Range: 10°C...60°C

Product Number	CU.P/NO	Length+/- (mm)	Packing
301-16-447	RND 765-00032	1000+/-10mm	1pc/poly bag with single color printed RND Connect logo++ RND Label

NO	ITEM	DESCRIPTION	
C	CONNECTOR 2	DB 37P FEMALE NICKEL-PLATED	
B	CONNECTOR 1	DB 37P MALE NICKEL-PLATED	
A	CABLE	37C+1 28AWG(7X0.12BC) +D7X0.12BC +AL/MYLAR_OD8.0MM color:BEIGE	