



Product Number	CU.P/NO	Length+/- (mm)	Packing
301-16-452	RND 765-00037	1800+/-10mm	1pc/poly bag with single color printed RND Connect logo+ RND Label
301-16-453	RND 765-00038	1000+/-10mm	
301-16-454	RND 765-00039	3000+/-50mm	
301-16-455	RND 765-00040	5000+/-50mm	
301-16-456	RND 765-00041	6000+/-50mm	

NOTES:
 ELECTRICAL CHARACTER:
 1.100% OPEN&SHORTTESTING.
 2.ROHS and REACH COMPLIANT.
 3. Copper OD Toleranle +/- 0.02mm
 4.connector connection method: soldering.
 5.THIS PRODUCT INCLUDED THE RAW MATERIAL:
 PVC : COPPER WIRE : Gold-plated copper
 : nickel-plated copper : nickel plated Iron
 shell : PBT : solder wire
 Temperature Range: 10°C . .60°C

C	CONNECTOR 2	DB 25P MALE NICKEL-PLATED	
B	CONNECTOR 1	DB 25P MALE NICKEL-PLATED	
A	CABLE	25C+1 28AWG(7X0.12BC) +D7X0.12BC +AL/MYLAR OD7.0MM color:BERGE	
NO	ITEM	DESCRIPTION	