

SEM LED Electronic Horn



RND 430-00107 (24V)
RND 430-00109 (240V)



RND 430-00106 (24V)
RND 430-00108 (240V)

Dispositivo di segnalazione acustica e luminosa.

Acoustic and luminous warning device.

Dispositif de signalisation acoustique et lumineux.. Akustische

und leuchtende Signaleinrichtung

Dispositivo de señalización acústica y luminosa.

CUPOLA DOME DOME HAUBE CÚPULA	PC						
BASE BASE BASE SOCKET BASE	PC/ABS						
GUARNIZIONE GASKET JOINT DICHTUNG JUNTA	O-Ring EPDM						
COLORI DISPONIBILI AVAILABLE COLOURS COULEURS DISPONIBLES VERFÜGBARE FARBEN COLORES DISPONIBLES							
VOLTAGGIO VOLTAGE TENSION SPANNUNG TENSIÓN	24Vdc – 240Vac						
SERVIZIO OPERATION FONCTIONNEMENT BETRIEBSART FUNCIONAMIENTO	T: ON = 1min. OFF = 10min.						
CORRENTE NOMINALE CURRENT CONSUMPTION CONSOMMATION DE COURANT STROMAUFNAHME CONSUMO DE CORRIENTE	<table border="1"> <thead> <tr> <th></th> <th>24Vdc</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>mA (Max)</td> <td>65</td> <td>50</td> </tr> </tbody> </table>		24Vdc	240Vac	mA (Max)	65	50
	24Vdc	240Vac					
mA (Max)	65	50					
RESA ACUSTICA ACOUSTIC OUTPUT RENDEMENT ACOUSTIQUE SCHALLLEISTUNGSPEGEL SALIDA ACUSTICA	<table border="1"> <thead> <tr> <th></th> <th>24Vdc</th> <th>240Vac</th> </tr> </thead> <tbody> <tr> <td>dB(A)1m</td> <td>96</td> <td>92</td> </tr> </tbody> </table>		24Vdc	240Vac	dB(A)1m	96	92
	24Vdc	240Vac					
dB(A)1m	96	92					
GRADO IP IP RATING DEGRE IP SCHUTZART GRADO IP	IP43						
TEMPERATURA DI FUNZIONAMENTO OPERATING TEMPERATURE TEMPERATURE DE SERVICE BETRIEBSTEMPERATUR	-30°C+50°C						

SEM LED Electronic Horn



TEMPERATURA DE FUNCIONAMIENTO

CERTIFICAZIONI, OMOLOGAZIONI

CERTIFICATIONS, APPROVALS CERTIFICAZIONI,
HOMOLOGATIONS PRODUKTZERTIFIKATE,
ZULASSUNGEN CERTIFICADOS, HOMOLOGACIONES

CE, UKCA

FISSAGGIO

MOUNTING
FIXATION
FIXIERUNG
FJACI3N

Viti

Screws
Vis
Schrauben
Tornillos

DISEGNO

TECHNICAL DRAWING
DESSIN
TECHNISCHE ZEICHNUNG
DIBUJO TECNICO

