



D2028 Pump Specifications

Free Flow Range.....	12-15LPM
Vacuum Range.....	0-16"Hg
Pressure Range.....	0-32PSI
Standard Motor Voltage Options.....	12VDC
Power.....	12W
Motor Construction Option.....	Iron Core-Oil Bearing
Diaphragm Material Option.....	EPDM
Operating Temperature Range.....	32°-120°F (0°-50°)

