

Professionally approved products.

Impact Wrenches

1/2 inch Compact Air Impact Wrench

RS Stock No. 739-8379



Specifications:

Power source : Compressed air
Maximum permissible operating pressure : 90 psi (6.2 bar)

Recommended operating pressure : 90 psi (6.2 bar)
Material : Aluminium

Size : 1/2"

Max Torque : 540Nm / 400 ft-lb

Vibration : 1.39m/s² Sound : 96.6dBA

Mechanism : Pin Clutch Hammer

Free Speed : 7,500RPM
Length : 7.5" / 190mm
Weight : 2.4kgs / 5.3lbs Min

Hose Size : 3/8" / 10mm

Air Inlet thread : 1/4"

Ave Air Consumption : 3.6cfm / 101.7 l/min Recommended lubrications : 10 Weight SAE Oil

Declaration of Conformity

We RS Components Ltd declare under our sole 739-8379-3/4" Impact Wrench responsibility that the conforms with the directive 2006/42/EEC and the standards EN 792-6 ISO 28927

Features:

- High power output
- Pin clutch hammer mechanism
- Forward and reverse mode
- Rear exhaust through handle
- 3 forward & 3 reverse operating impact settings
- Non slip comfortable grip
- Ideal for truck, bus and farm machinery work
- Rugged design
- Single handed direction change

