

FEATURES

- Low cost
- Compact and lightweight
- Dual LCD display
- Air flow calculate function
- Sampling rate 1 time per second

RS PRO IM-740 Rotary Vane 25m/s Max Air Velocity Air Velocity, Temperature Anemometer

RS Stock No.:106-5314



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

From the trusted RS PRO brand, a mini rotating vane anemometer designed for measuring air velocity, wind speed and temperature. The digital hand-held meter provides rapid accurate readings without compromising on performance. Constructed from high-quality impact resistant materials this RS RRO pocket sized meter is ideal for engineers and HVAC technicians for on the spot measurements.

General Specifications

| Model Number | IM-740 | |
|------------------------|---|--|
| Measurement Parameters | Air Velocity, Temperature | |
| Probe Type | Rotary Vane | |
| Display Type | Dual LCD display | |
| Auto Power Off | Yes | |
| Data Hold | Yes | |
| Data Storage | No | |
| Accessories | Manual, batteries and carrying bag | |
| Application | HVAC, Construction, Roofing, Sailing, boating and windsurfing, Climbing and hiking, Aviation, wind direction, airflow and gust, Weather stations and meteorological studies | |

Measurement

| Parameters | Range | Resolution | Accuracy |
|----------------------|---------------|------------|------------------|
| Air Velocity (m/s) | 0.4 – 25.00 | 0.1 | ±(2%+0.2 m/s) |
| Air Velocity (Km/h) | 1.5 – 90.0 | 0.1 | ±(2%+0.8 km/h) |
| Air Velocity (mph) | 0.9 - 55.0 | 0.1 | ±(2%+0.4 mph) |
| Air Velocity (Knots) | 0.8 - 48.0 | 0.1 | ±(2%+0.4 knots) |
| Air Velocity (fpm) | 79 – 4921 | 1 | ±(2%+40 ft./min) |
| Temperature | -20°C to 50°C | 0.1°C | ±1% |



Electrical Specifications

| Operating Supply Voltage | Battery |
|--------------------------|---------|
| Batteries Included | YES |
| Battery Type | AAA |
| Battery Life | 50hours |

Mechanical Specifications

| Impeller Diameter | 30mm |
|-------------------|---------------------|
| Dimensions | 135mm x 48mm x 23mm |
| Width | 48mm |
| Length | 135mm |
| Height | 23mm |
| Weight | 80g |

Operation Environment Specifications

| Minimum Operating Temperature | -20°C |
|-------------------------------|-------|
| Maximum Operating Temperature | 50°C |



