

## Features

- Versatile single layer foam anti-fatigue mat.
- Insulates standing workers against the effects of cold concrete floors. Lightweight, so easy to transport and reposition.
- Best suited to dry environments.
- High visibility version available with bright yellow borders.
- Ideal for lighter industrial use.
- Industrial-look diamond surface pattern.
- Available in mats and rolls.
- Fire tested to BS EN 13501-1.

## RS PRO Diamond pattern anti-fatigue mat for dry workplaces

RS Stock No.: 159-6172



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

*An open cell PVC foam anti-fatigue suitable for use in dry environments. Designed with a Diamond pattern the Anti-fatigue mat is manufactured from a single layer of foam and provides comfort and protection to workers from cold surfaces over extended periods of time.*

- Lightweight and easy to reposition the foam mat is anti-slip and provides excellent cold insulation on cold floors such as concrete, reduces noise and enhances safety.*

## General Specifications

Material	Open Cell PVC (Foam)
Surface Finish	Diamond pattern
Min. Operating Temperature	0°C
Max. Operating Temperature	+60°C
Environmental Resistance	Suitable for dry indoor environments
Typical Applications	Production lines, Assembly areas, Packing stations, Workbenches
Installation Method	Loose lay
Cleaning Method	Brush/mop the top surface
Fire Tested to	BS EN 13501-1 Class Dfl - s1
Guarantee	1 year when used in a dry environment
Adhesive recommended by F.Ball for permanent bond	F44
Tackifier recommended by F.Ball	F41
Adhesive recommended by F.Ball for heavy-duty/wet areas	F74, F81, F84

## Mechanical Specifications

Product Height	9.5 mm
Size of Safety Border	100 mm