

Features

- TUV/GS/S/CE Certified
- Schuko extn switched socket 6 way 2m
- 2 meter, H05VV-F, 3G1.5MM cable

RS PRO Schuko extn switched socket 6 way 2m

RS Stock No.: 222-2591



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- This range of RS PRO extension leads have been tried and tested to the highest standards, made from high quality material and are suitable for many applications. From RS PRO, this schuko extension switched socket is ideal for extending power to where you need it. With a schuko socket, this European type extension cord can be used in most European countries.*

General Specifications

Operating Temperature	20 ~ +80°C (-4 ~ 176°F)
Socket Type	Schuko

Electrical Specifications

Electrical Rating	16A 250V
Dielectric Strength	1000VAC for 1 min between current carrying parts 2500VAC for 1 min between non-current carrying parts

Protection Category

Degree of Protection	IP20/NEMA1
----------------------	------------