



ENGLISH

Datasheet

RS PRO Line Mounting Hydraulic Flow Control Valve, G 3/8, 350 bar

RS Stock No 243-5587:

High Pressure Flow Control Valve

High pressure flow control valves for general purpose use in a hydraulic system.

Features and Benefits

- Double acting needle
- Easy to read colour flow graduation scale and a locking screw to stabilise flow
- Nitrile rubber seals
- Temp. range -10 to +100°C
- 0.5 bar cracking pressure



Attribute	Value
Manufacturer Series	NDRV
Connection Port Thread	G 3/8
Maximum Flow Rate	75L/min
Body Material	Steel
Seal Material	Nitrile Rubber
Maximum Operating Pressure	350 bar
Thread Size	3/8in
Thread Standard	G
Maximum Operating Temperature	+100°C
Minimum Operating Temperature	-10°C