

Features

- Continuous Sound output
- 80-95dB
- Weather proof
- 4-28VDC
- 30mm Panel mount
- Low power consumption
- No moving parts

RS PRO Electronic Sounder - Continuous Audible Alarm

RS Stock No.: 2712242



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A panel mount Audible Alarm with a Continuous electronic sound output, suitable for general alarm applications. With an operating voltage between 4VDC and 28VDC, the Alarms draw 3-15mA current. They produce a Continuous type tone, between 80-95dB which is an attention-grabbing Sound that can be heard clearly from a distance. Compact in design and with a single hole panel mount fixing they are simple and easy to install. Supplied with a 6.35mm bladed terminal with a screw connection the Alarms can be connected either by the screw terminal or a faston connection.

General Specifications

Sound Type (Tone)	Continuous
Sound Level	80-95dB
Construction	Weatherproof
Mounting	30mm Through Hole Panel Mount
Colour	Black
Frequency	2900 Hz
Driver	Internal Solid State Circuitry
Termination	0.8 x 6.35mm tinned brass Male terminals tapped and fitted with plated steel screws.

Electrical Specifications

Minimum Supply Voltage	4VDC
Maximum Supply Voltage	28VDC
Current Type	DC
Rated Voltage	24VDC
Current Consumption	3-15mA

Mechanical Specifications

Dimensions	42.9 (dia) x 43 (l) mm
Diameter	42.9mm
Length	43mm
Mounting Style	Panel Mount with Locking Ring

Operation Environment Specifications

Maximum Temperature	-30°C
Minimum Temperature	+60°C

Approvals

Compliance/Certifications	CE / UKCA
Standards Met	RoHS Compliant

