

## Features

- Pulsating Sound output
- 80-95dB
- Weather proof
- 4-28VDC
- 30mm Panel mount
- Low power consumption
- No moving parts

## RS PRO Electronic Sounder - Pulse Audible Alarm

RS Stock No.: 2712245



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

A panel mount Audible Alarm with a Pulsating electronic sound output, suitable for general alarm applications. With an operating voltage between 4VDC and 28VDC, the Alarms draw 3-15mA current. They produce a Pulsating type tone, between 80-95dB which is an attention-grabbing Sound that can be heard clearly from a distance. Compact in design and with a single hole panel mount fixing they are simple and easy to install. Supplied with a 6.35mm bladed terminal with a screw connection the Alarms can be connected either by the screw terminal or a faston connection.

## General Specifications

<b>Sound Type (Tone)</b>	Pulsating
<b>Sound Level</b>	80-95dB
<b>Construction</b>	Weatherproof
<b>Mounting</b>	30mm Through Hole Panel Mount
<b>Colour</b>	Black
<b>Frequency</b>	2900 Hz
<b>Driver</b>	Internal Solid State Circuitry
<b>Termination</b>	0.8 x 6.35mm tinned brass Male terminals tapped and fitted with plated steel screws.

## Electrical Specifications

<b>Minimum Supply Voltage</b>	4VDC
<b>Maximum Supply Voltage</b>	28VDC
<b>Current Type</b>	DC
<b>Rated Voltage</b>	24VDC
<b>Current Consumption</b>	3-15mA

## Mechanical Specifications

<b>Dimensions</b>	42.9 (dia) x 43 (l) mm
<b>Diameter</b>	42.9mm
<b>Length</b>	43mm
<b>Mounting Style</b>	Panel Mount with Locking Ring

## Operation Environment Specifications

<b>Maximum Temperature</b>	-30°C
<b>Minimum Temperature</b>	+60°C

## Approvals

<b>Compliance/Certifications</b>	CE / UKCA
<b>Standards Met</b>	RoHS Compliant

