

Features

- Swivel-in sliding block profile for self-assembly of individual fastening elements
- The swivel-in sliding block for inserting directly at the installation position for easy assembly
- The swivel-in sliding block with spring can be inserted directly at the assembly point and fixed in position thanks to attached springs
- The swivel-in sliding block with headless setscrews permits shake-proof fixing in all positions

RS PRO Connecting Component, Sliding Block Type, M8 Thread

RS Stock No.: 2768166



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

Looking for a fast and uncomplicated solution for attaching construction components to an aluminium extrusion? Look no further than RS PRO's sliding block. Its simple swivel-in insertion process ensures effortless assembly within an 8mm groove. With headless setscrews and an integrated spring, it provides reliable and vibration-resistant fastening in any orientation once installed. This ensures the structural integrity of your connections, even in demanding conditions.

- *Standard M5 thread size offers widespread compatibility*
- *Reliably absorbs high forces, so can cope with demanding settings and vibrations*
- *Suitable for Manufacturing equipment, Machine guards and Architecture industry*

General Specifications

Product Family	RS Structural System
Product System	
Structural Element Type	Fixing & Connecting Element
Connector Type	Sliding Block
Material	Steel
Finish	Galvanised
Applications	It's mostly used for accessories or connections of other profiles

Mechanical Specifications

Fits Groove Size	Slot 8mm
Thread Size	M8
Length	16mm
Fits Strut Profile	30 mm

Protection Category

ESD-capable	No
-------------	----

Classification

eCl@ss Version	
UNSPSC Version	

