

FEATURES

- Momentary foot switch controller
- Die-cast aluminium body for durability
- Single pole momentary changeover contact rated at 240V, 3A.
- 9mm rubber gland cable entry
- Suited for medium/heavy duty industrial applications
- Designed to reduce operator fatigue
- Operating Temperature: -5°C to 40°C

RS PRO General Industrial Momentary Foot Switch - Die Cast Aluminium Case Material, SP-CO, 6 A Contact Current, 250V

RS Stock No.: 321-060



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO medium duty foot switches which are ideal for general industrial applications This foot switch is constructed from die-cast aluminium making it tough and durable for harsh environments and is black in colour.

General Specifications

Contact Configuration	SP-CO
Switch Operation	Momentary
Case Material	Die Cast Aluminium
Switch Environment	General Industrial
Contact Material	Silver
Colour	Black
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Voltage Rating (DC)	24V
Contact Current Rating	6A

Mechanical Specifications

Length	152mm
Height	46mm
Dimensions	152mm x 94mm x 46mm
Width	94mm

Operation Environment Specifications

Operating Temperature	-5°C to 40°C
------------------------------	--------------

Protection Category

IP Rating	IPX2
------------------	------

Approvals

Standards Met	2006/95/EC, EN 60950
Compliance/Certifications	EN 61058-2-1; EN 61058; EN 60601-1; EN 60950, RoHS





Outline Dimensions

