

Features

- High quality nylon tyre
- Swivel castors
- Non-slip rubber feet
- Vibration damping rubber feet.

RS PRO Swivel Castor, 250kg Load Capacity, 63mm Wheel Diameter

RS Stock No.: 611-4458



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

RS PRO castors are a range of multifunction levelling castors. These wheels are versatile and area ideal choice for equipment that needs to be mobile, but when in place is completely firm and stationary. They can be used in numerous applications such as Vending machines, Medical appliances and Workstations. The plate is steel with a khaki powder coating whilst the bracket is aluminium die-casting, also featuring bi-level balls upon balls for full swivel.

General Specifications

Rotation	Swivel
Weight Class	Heavy Duty
Load Capacity (Static)	500kg
Load Capacity (Dynamic)	250kg
Load Capacity / 4pcs	1000kg
Tyre Material	Nylon
Hub Material	Nylon
Hardness of Thread	70 Shore D
Includes Brake	No
Features	Corrosion Resistant, Impact Resistant, Shock Absorbing
Applications	Vending machines, Medical appliances, Workstations, Measuring Instruments

Mechanical Specifications

Mounting Type	Plate
Wheel Diameter	63mm
Wheel / Tread Width	30mm
Overall Height	103mm
Number of Fixing Holes	4
Fixing Hole Size	9mm

Hub Bearing Type	Ball Bearing
Levelling Extent	15mm
Offset	46mm

Fixing Centres Specifications

Fixing Centres	90mm x 90mm
Fixing Centres (Length)	90mm
Fixing Centres (Width)	90mm

Fixing Plate Specifications

Fixing Plate Dimensions	70mm x 70mm
Fixing Plate Length	70mm
Fixing Plate Width	70mm

Operation Environment Specifications

Operating Temperature	-10°C to 90°C
-----------------------	---------------



Drawings

