

Features

- Material: UL approved Nylon 66, 94V-2
- Color: White.
- Suit a variety of applications, and diverse industries.
- Function :Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal, and then tighten up the nut to hold cables in position.
- Simply and quickly fixed, high degree of the protection IP68 preventing dust and water.

RS PRO Cable Gland

RS Stock No.: 6694642



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

- *Material: UL approved Nylon 66, 94V-2*
- *Color: Black, available in other colors.*
- *Suit a variety of applications, and diverse industries.*
- *Function :Mount gland to pre-drilled panel hole, use locknut to fix gland on board, insert the cables in the seal,and then tighten up the nut to hold cables in position.*
- *Feature : Simply and quickly fixed, high degree of the protection IP68 preventing dust and water.*
- *Available to order the accessories separately. Follow the drawing and add the letter to the suffix part number, L for locknut, W for washer, B for gland body, S for seal, N for nut.*

General Specifications

| | |
|-------------------------------|--------------------|
| Series | Metric Thread |
| Type | Cable Gland |
| Colour | White |
| Material | Nylon 66 |
| UV Resistant | No |
| Minimum Operating Temperature | -40°C |
| Maximum Operating Temperature | 85°C |
| Fire Behaviour | Self-Extinguishing |
| Quantity | 25pcs |

Mechanical Specifications

| | |
|-------------------|-------------|
| Thread | M12 x P1.25 |
| Mounting Hole | 12 + 0.2 mm |
| Cable Range | 3 ~ 6.5 mm |
| Thread Length(L1) | 7.9mm |

Protection Category

| | |
|-----------|------|
| IP Rating | IP68 |
|-----------|------|

Approvals

| | |
|---------------|------------------------------------|
| Standards Met | RoHS Certificate of compliance, CE |
|---------------|------------------------------------|

