



CWT2-B

SOLDERSLEEVE WIRE SPLICE BLUE, OD MAX=4.4mm, 1.8-2.5mm² (AWG 18-12)

Product Properties:

Colour	Blue
Operating temperature	-55-125 °C
Connector type	Lödskarvhylsa, dubbelring
Packaging	Loose piece

Dimensions:

MOQ	50 .
Unit	pcs
Nominal cross section	1.8-2.5 mm ²

Approvals:

Compliance:

Conflict minerals	Contains minerals possible originate from conflict mines that the supplier cannot identify nor has not given any details about the source of the minerals
Iron and Steel Sanction	Complied
Link to manufacturer COC	https://www.te.com/commerce/alt/SinglePartSearch.do?PN=493995-000
Reach	Yes. CAS 7439-92-1, 32 %, CAS 7440-43-9, 18 %
RoHS	No
SCIP	5baad761-bcf9-4b10-a101-a5e67076a58f

Other information:

ETIM-Class	EC000466 - Heat-shrink crimp connection
------------	-----------------------------------------

ETIM-Release	7.0
Trademark	TE Connectivity
Product Group	Soldersleeve wire splices
Search Description	493995-000, B-008-14
Alternative SKU	CWT2-B

Logistic information:

Barcode	733117640019
Country of origin	MX
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	50 .
Packaging	Loose piece
Stock code	CWT2-B
Taric code	85369010
Unit	pcs