



## CWT2-R

SOLDERSLEEVE WIRE SPLICE RED, OD MAX=2.8mm, 0.6-2.0mm<sup>2</sup> (AWG 22-18)

### Product Properties:

Colour	Red
Operating temperature	-55-125 °C
Connector type	Lödskarvhylsa, dubbelring
Packaging	Loose piece

### Dimensions:

MOQ	50 .
Unit	pcs
Nominal cross section	0.6-2 mm <sup>2</sup>

### Approvals:

### Compliance:

Conflict minerals	Contains minerals possible originate from conflict mines that the supplier cannot identify nor has not given any details about the source of the minerals
Iron and Steel Sanction	Complied
Link to manufacturer COC	<a href="https://www.te.com/commerce/alt/SinglePartSearch.do?PN=747081-000">https://www.te.com/commerce/alt/SinglePartSearch.do?PN=747081-000</a>
Reach	Yes. CAS 7439-92-1, 32 %, CAS 7440-43-9, 18 %
RoHS	No
SCIP	9edec777-e6c2-4a86-b7cd-5079b95b83ef

### Other information:

ETIM-Class	EC000466 - Heat-shrink crimp connection
------------	---

<b>ETIM-Release</b>	7.0
<b>Trademark</b>	TE Connectivity
<b>Product Group</b>	Soldersleeve wire splices
<b>Search Description</b>	747081-000, B-008-13
<b>Alternative SKU</b>	CWT2-R

### **Logistic information:**

<b>Barcode</b>	733117640020
<b>Country of origin</b>	MX
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	50 .
<b>Packaging</b>	Loose piece
<b>Stock code</b>	CWT2-R
<b>Taric code</b>	85369010
<b>Unit</b>	pcs