

Rittal – The System.

Faster – better – everywhere.

► **Component shelf,
static installation for
482.6 mm (19")
system punchings,
depth-variable for TS
IT, TE – DK 5501.655**

Date : Oct 31, 2016

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



Component shelf, static installation for 482.6 mm (19") system punchings, depth-variable for TS IT, TE – DK 5501.655

created: 31.10.2016 on www.rittal.com/com-en



Product description

Benefits:	Tool-free, time-saving one-man assembly
Applications:	Depth-variable to adapt to individual distances between levels
Material:	Sheet steel
Surface finish:	Spray-finished
Colour:	RAL 9005
Supply includes:	Assembly parts

Product features

To fit:	Enclosure type: TS IT Enclosure type: TE 7000 Enclosure type: TE 8000
Dimensions:	Width: 484 mm
Installation options:	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear
Distance between levels:	min.: 400 mm max.: 600 mm

Units:	0.5 U
Load capacity:	50 kg
Packs of:	1 pc(s).
Weight/pack:	6.56 kg
EAN:	4028177679092
Customs tariff number:	73269098
ETIM 6.0:	EC002620
ETIM 5.0:	EC002620
eCl@ss 8.0/8.1:	27189261
eCl@ss 7.0/7.1:	27189261
eCl@ss 6.0/6.1:	27189261
eCl@ss 5.1/5.1.4:	27189218