




|     |        |               |      |           |         |
|-----|--------|---------------|------|-----------|---------|
| LTR | Rev.No | Revisior note | Date | Signature | Checked |
|-----|--------|---------------|------|-----------|---------|

MINI DIN6 MALE  
INSULATOR:GREEN




MOLDED TYPE  
COLOR: GREEN

USB A JACK  
INSULATOR:WHITE



CONFIGURATION:

MD6M                      USB A JACK



NOTE:

1. OVER ALL MOLDED WITH GREEN PVC
2. JUMP WIRE:4C+1
3. TEST: OPEN/SHORT 100% TEST

|  |        |        |                   |       |       |            |    |
|--|--------|--------|-------------------|-------|-------|------------|----|
| RANGE                                    | 0~10   | 11~25  | 26~40             | 41~60 | 61~80 | 81~100     | X  |
| TOLERANCE(±)                             | 0.10   | 0.15   | 0.20              | 0.25  | 0.30  | 0.35       | 2% |
| TITLE:<br>MD6M/USB A JACK<br>MOLDED TYPE |        | Buyer  | Date              | Unit  | Rev.  | Dwg. no.   |    |
|  |        | ROC    | 4.JAN.06          | mm    | 2.0   | 12.99.1072 |    |
| DRN BY                                   | CHK BY | APC BY | ROTRONIC CO., LTD |       |       |            |    |
|  |        |        |                   |       |       |            |    |