

# ROLINE Industrial Switch, 8x RJ-45, unmanaged

<b>Product No.</b>	21.13.1156
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	21.13.1156
<b>EAN (single piece)</b>	7611990189168



- Fast Ethernet switch with 8 shielded 10/100 Base-T copper ports
- Wide operating temperature range for temperature critical environment
- Auto MDI/MDI-X crossover function
- Supports IEEE 802.3x flow control for full-duplex operation
- Supports Back-pressure flow control for half-duplex operation
- Supports DIN-rail mounting
- Power: Input: 5 - 30V DC, Consumption: 2.3W (max.)
- Operating Temperature: - 10 °C - +70 °C
- DC Input via terminal block or DC power jack (6.3mm / 2.0mm)
- Dimensions: 40 x 80 x 95 mm (WxDxH)
- As according power supply we recommend 21.13.1226
  
- Contents: Switch

## Technical specifications

Manufacturer	ROLINE
Product group	Network Switches
Product type	Fast Ethernet Switch
Colour	black
Network standard	Fast Ethernet
LAN (Mbps)	10/100

Quantity of ports	8
Fast Ethernet Ports RJ-45	8
Mounting form	DIN Rail
Management	No
Stackable	No
Technical particularity	- 10 °C - +70 °C
Dimensions (HxWxD)	95 x 40 x 80 mm
Power supply unit (internal/external)	External