

ROLINE Industrial Switch, 16x RJ-45, unmanaged

Product No.	21.13.1157
Manufacturer	ROLINE
Manufacturer No.	21.13.1157
EAN (single piece)	7611990133635



- Fast Ethernet switch with 16 shielded 10/100 Base-T copper ports
- Wide operating temperature range for temperature critical environment
- Auto MDI/MDI-X crossover function
- Supports IEEE 802.3x flow control for full-duplex operation
- Supports Back-pressure flow control for half-duplex operation
- Supports DIN-rail mounting and panel mounting
- Power: Input: 4.5 - 50V DC, Consumption: 3.4W (max.)
- Operating Temperature: - 20 °C - +70 °C
- DC Input via terminal block or DC power jack (6.3mm / 2.0mm)
- Dimensions: 140 x 106 x 40 mm (WxDxH)
- As according power supply we recommend 21.13.1226
- Contents: Switch

Technical specifications

Manufacturer	ROLINE
Product group	Network Switches
Product type	Fast Ethernet Switch
Colour	black
Network standard	Fast Ethernet
LAN (Mbps)	10/100
Quantity of ports	16

Fast Ethernet Ports RJ-45	16
Mounting form	DIN Rail
Management	No
Stackable	No
Technical particularity	- 20 °C - +70 °C
Dimensions (HxWxD)	140 x 40 x 106 mm
Power supply unit (internal/external)	External