

ROLINE Gigabit Ethernet Switch, 8x RJ-45, unmanaged

Product No.	21.14.3521
Manufacturer	ROLINE
Manufacturer No.	21.14.3521
EAN (single piece)	7611990144846



This switch allows high-speed networking on a Gigabit Ethernet basis with 8 TP ports.

- Provides 8 10/100/1000Mbps Gigabit Ethernet ports
- All 10/100/1000M ports support auto-negotiation and auto-MDI/MDI-X detection
- Supports full/half-duplex transfer mode for 10/100Mbps
- Supports full-duplex transfer mode for 1000Mbps
- Store-and-Forward switching method
- Wire-speed packet filtering and forwarding rate
- Supports IEEE 802.3x flow control
- Supports Jumbo Frame up to 9.6K bytes
- MAC Address Table: 8K
- Buffer Memory: 256K bytes
- LED Indication
- Environment Operating Temperature: 0°C ~ 40°C (main device)
- Dimensions (WxDxH): 155 x 86 x 26 mm

Technical specifications

Manufacturer	ROLINE
Product group	Network Switches
Product type	Gigabit Ethernet Switch

Colour	black
Scope of delivery	Switch, power supply (5V DC, 1A), manual
Network standard	Gigabit Ethernet
LAN (Mbps)	10/100/1000
Quantity of ports	8
Gigabit Ethernet Ports RJ-45	8
Stackable	No
Dimensions (HxWxD)	155 x 86 x 26 mm
Power supply unit (internal/external)	External