

# ROLINE External Type M.2 NVMe SSD Enclosure with USB 3.2 Gen 2x2 Type C

|                           |               |
|---------------------------|---------------|
| <b>Product No.</b>        | 16.01.4147    |
| <b>Manufacturer</b>       | ROLINE        |
| <b>Manufacturer No.</b>   | 16.01.4147    |
| <b>EAN (single piece)</b> | 7630049617544 |



## Extra narrow empty housing made of matt aluminium for M.2 SSDs, for connection via USB 3.1 / USB 3.2 Gen 2 Type C

- Empty housing for M.2 SSDs with USB Type C connector
- External interface: USB type C
- Compatible with USB 3.1 / USB 3.2 Gen 2x2 with data transfer rates up to 20 Gbps
- Supports M.2 SSDs 2230, 2242, 2260, 2280 (M key)
- Matt, silver aluminium housing

Note: According to the current specifications of USB.org we have adapted the technical data of our USB 3 products. The new designation for the already known USB specifications has been changed to USB 3.2 Gen 1 (formerly USB 3.0 / USB 3.1 Gen 1) and USB 3.2 Gen 2 (formerly USB 3.1 / USB 3.1 Gen 2).

### Technical specifications

|                    |   |
|--------------------|---|
| Manufacturer       | ROLINE                                      |
| Product group      | Drive housing                               |
| Product type       | M.2 SSD Enclosure                           |
| Colour             | anthracite                                  |
| Scope of delivery  | M.2 SSD Enclosure, manual, USB Type C cable |
| Quantity of Drives | 1   |
| Drive form         | M.2   |

|                                       |                         |
|---------------------------------------|-------------------------|
| External connections                  | USB 3.2, Gen2x2, Type C |
| Dimensions (HxWxD)                    | 15 x 46 x 118.5 mm      |
| Material (casing)                     | Aluminium               |
| Power supply                          | over USB port           |
| Height                                | 15 mm                   |
| Width                                 | 46 mm                   |
| Depth                                 | 118.5 mm                |
| Weight                                | 129 g                   |
| Height of packaging<br>(single piece) | 20 mm                   |
| Width of packaging<br>(single piece)  | 100 mm                  |
| Depth of packaging<br>(single piece)  | 100 mm                  |
| Package weight (single<br>piece)      | 0.02 kg                 |