

ROLINE Fibre Optic Jumper Cable Duplex, 9/125µm, OS2, LC/LC, Steel Armored, white, 15 m

Product No.	21.15.8636
Manufacturer	ROLINE
Manufacturer No.	21.15.8636
EAN (single piece)	7630049621848



ROLINE LSOH fiber optic patch cable with single mode fibers in OS2 quality.

- Cable sheathing made of halogen-free, low smoke and flame-retardant material
- Assembled with high-quality connectors with ceramic ferrule
- Core structure: Duplex cable I-VH
- High tensile strength due to aramid yarn strain relief
- Steel armored
- Compared to standard fiber optic patch cables, these cables are additionally protected by a flexible steel spiral helix
- Due to this high-quality cable construction, FO cables are tread-resistant and suitable for applications with increased mechanical demands
- Only suitable for indoor use

Technical specifications

Manufacturer	ROLINE
Product group	Fibre optic cable
Product type	Fibre Optic Jumper Cables Singlemode
Colour	white
Length	15 m
Quantity of fibre	2
Cable type	Duplex Cable

External cable	No
Fibre section	9/125µm OS2
Connection ports	LC / LC
Side 1 Connector Type	LC
Side 2 Connector Type	LC
Colour (Cable)	white
Aramid strain relief	Yes
Cable LSOH	Yes
Armouring	Yes
Weight	14.1 g
Height of packaging (single piece)	30 mm
Width of packaging (single piece)	160 mm
Depth of packaging (single piece)	180 mm
Package weight (single piece)	0.4 kg