

ROLINE Cat.6 (Class E) 19" Patch Panel, 24 Ports, UTP, grey

Product No.	26.11.0355
Manufacturer	ROLINE
Manufacturer No.	26.11.0355
EAN (single piece)	7611990156511



- The ROLINE Cat.6/Class E 19" patch panel fulfils the Cat.6/Class E Permanent Link Standard and is ideal for Gigabit Ethernet networks
- Cable assembly takes place using LSA-plus piercing terminals with colour coding on the top in accordance with EIA/TIA 568
- 24 ports
- Colour: Light grey

For a structured cabling system we recommend to use the following components:

- ROLINE Cat.6 UTP Cable, Solid Wire, AWG23: 21.15.0990 (100 m), 21.15.0991 (300 m)
- ROLINE Cat.6 Flush Mount Wall Jack, unshielded: 25.16.8494 (white), 25.16.8500 (ivory)
- ROLINE Cat.6 Surface Mount Wall Jack, unshielded: 25.16.8394 (white), 25.16.8395 (ivory)
- ROLINE Cat.6 19" Patch Panel, 24 Ports, unshielded: 26.11.0355 (light grey), 26.11.0362 (black)
- ROLINE Cat.6 UTP Patch Cord, grey, 5 m: 21.15.0935

Our in-house laboratory has tested this cable-plug combination, in a Channel of 100 meters, in compliance with Class E specifications.

Technical specifications

Manufacturer	ROLINE
Product group	Connection technology TP
Product type	Patchpanel Cat.6 / Class E

Colour	grey
Shield type	Not screened
Transfer quality	Cat6 / Class E
Cabinet system	19"-Technique
Quantity of ports	24
Assembly cable connection	Krone LSAprus
Assignment	EIA/TIA 568A & 568B
Modular assembly	No
Shield contacts	No
separate strain relief	Yes
Connection direction	Straight
Height units	1 UH
Height	44 mm
Width	482.6 mm
Depth	109 mm
Weight	874.3 g
Height of packaging (single piece)	80 mm
Width of packaging (single piece)	150 mm
Depth of packaging (single piece)	490 mm
Package weight (single piece)	2.2 kg