

ROLINE Cat.6 (Class E) 19" Patch Panel, 24 Ports, STP, black

Product No.	26.11.0361
Manufacturer	ROLINE
Manufacturer No.	26.11.0361
EAN (single piece)	7611990182435



- The ROLINE Cat.6/Class E 19" patch panel fulfils the Cat.6/Class E Permanent Link Standard and is ideal for Gigabit Ethernet networks
- Cable assembly takes place using LSA-plus piercing terminals with colour coding on the top in accordance with EIA/TIA 568
- Sheet steel housing and cover
- 24 ports
- Colour: Black

For a structured cabling system we recommend to use the following components:

- ROLINE Cat.6 S/FTP Cable, Solid Wire, AWG23: 21.15.0890 (100 m), 21.15.0891 (300 m)
- ROLINE Cat.6 Flush Mount Wall Jack, shielded: 25.16.8492 (white), 25.16.8493 (ivory)
- ROLINE Cat.6 Surface Mount Wall Jack, shielded: 25.16.8392 (white), 25.16.8393 (ivory)
- ROLINE Cat.6 19" Patch Panel, 24 Ports, shielded: 26.11.0351 (light grey), 26.11.0361 (black)
- ROLINE Cat.6 S/FTP Patch Cord, grey, 5 m: 21.15.0835

The accredited German laboratory GHMT has tested and certified this product combination, in a Channel of 100 meters, as being compliant to Class E specifications; certificate no. z2365b-10-E (with flush

Technical specifications

Manufacturer	ROLINE
Product group	Connection technology TP

Product type	Patchpanel Cat.6 / Class E
Colour	black
Shield type	Screened
Transfer quality	Cat6 / Class E
Cabinet system	19"-Technique
Quantity of ports	24
Assembly cable connection	Krone LSAplus
Assignment	EIA/TIA 568A & 568B
Modular assembly	No
Material (casing)	Metal
Shield contacts	Yes
separate strain relief	Yes
Connection direction	Straight
Height units	1 UH
Height	44 mm
Width	482.6 mm
Depth	109 mm
Weight	1504.5 g
Height of packaging (single piece)	70 mm
Width of packaging (single piece)	150 mm
Depth of packaging (single piece)	560 mm
Package weight (single piece)	1.69 kg