

Category 6 Keystone Panel Mount Coupler



Category 6 Keystone Panel Mount Coupler (SACK2, SACK2bk-24)

Features

- Designed to fit US industry standard keystone mount outlets wall plates and patch panels
- High performance data throughput, meets Category 6 data transfer rates
- Shielded and Category 5e versions also available
- Fully loaded 19 inch panel also available

Packaging


• Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK2bk-24 is available as a "bulk pack" of 24 pieces without individual bags.

Specifications

Dimensions SACK2: 29.5x16.9x19.25 mm
SACK2bk-24: 280x70x35mm

Weight SACK2: 6 grams
SACK2bk-24: 138 grams

- Packaging: Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK2bk-24 is available as a "bulk pack" of 24 pieces without individual bags
- Housing: ABS UL94V-0
- Contacts: 50μ"/1.27μm gold plating over nickel plated phosphor bronze
- Colour: White (SACK2wh) or black (SACK2bk)





Category 6 Keystone Panel Mount Coupler (Shielded)



Category 6 Keystone Panel Mount Coupler Shielded (SACK3S, SACK3S-24)

Features

- Designed to fit US industry standard keystone mount outlets wall plates and patch panels
- RJ45 complies with FCC68
- High performance data throughput, meets Category 6 data transfer rates
- Operating temperature: ~40°C ~ +60°C
- Jack insertion life > 750 mating cycles
- Available as part of our innovative Panel Mount and D UNIVERSAL ranges

Packaging:

• Standard product is supplied in individual polythene bags. To save time for panel assemblers, SACK3S-24 is available as a "bulk pack" of 24 pieces without individual bags.

Specifications

Dimensions

SACK3S: 29.7 x 17 x 19.25 mm approx. **SACK3S-24**: 280 x 70 x 35mm approx.

Materials:

Housing: Nickel plated zinc alloy Contacts: 50μ "/ 1.27 μ m gold plating over nickel plated phosphor bronze Earthing lug material: Stainless steel SUS304

Weight:

SACK3S: 18g approx. SACK3S-24: 460g approx.

