

# Product data sheet

Specifications



## APC Service Bypass Panel 200/208/230/240V 125A HW Input/ Output

SBP20KP

### Overview

Lead time Usually in Stock

### Main

**Main Input Voltage** 200 V  
208 V  
220 V  
230 V  
240 V  
380 V 3 phase  
400 V 3 phase  
415 V 3 phase

**Main Output Voltage** 200 V  
208 V  
220 V  
230 V  
240 V

**Output connector type** Hard Wire 3-wire (H N + E) 1  
Hard Wire 3-wire (2PH + G) 1

**Number of rack unit** 4U

**Number of cables** 1

**Provided Equipment** Installation guide  
Rack Mounting brackets  
User Manual

### Physical

**Color** Black

**Height** 7.01 in (17.8 cm)

**Width** 17.01 in (43.2 cm)

**Depth** 21.81 in (55.4 cm)

**Net Weight** 42.59 lb(US) (19.32 kg)

**Mounting Location** Front

**Mounting preference** Lower

**Mounting Mode** Rack-mounted

### Input

**Input Frequency** 50/60 Hz

**Number of input connectors** 1 Hard Wire 3-wire (H N + E)  
1 Hard Wire 3-wire (2PH + G)  
1 Hard Wire 5-wire (3PH + N + G)

Permissible voltage	200...240 V
Max line current	125 A
Input current limits	125 A
Load Capacity	20000 VA
Load Power Factor Range	0...1

## Output

Maximum Total Current Draw per Phase	125 A
Protection Type	Circuit breaker
Efficiency	99 %

## Conformance

Product Certifications	CSA GOST
------------------------	-------------

## Environmental

Ambient Air Temperature for Operation	-4...122 °F (-20...50 °C)
Relative Humidity	0...95 %
Operating altitude	0...15000 ft
Ambient Air Temperature for Storage	-40...149 °F (-40...65 °C)
Storage Relative Humidity	0...95 %
Storage altitude	0...50000 ft (0.00...15240.00 m)

## Ordering and shipping details

GTIN	731304266952
------	--------------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	12.01 in (30.5 cm)
Package 1 Width	33.27 in (84.5 cm)
Package 1 Length	24.02 in (61 cm)
Package 1 Weight	69.14 lb(US) (31.36 kg)

## Offer Sustainability

REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a>
RoHS exemption information	Yes

# Contractual warranty

---

Warranty 2 years (parts only)

Recommended replacement(s)