



**SC-3 0240**

E1441277

SPLICING CONNECTOR, 3-CONDUCTOR 0.2-2.5mm<sup>2</sup>(4mm<sup>2</sup> Solid), AWG 28-12, WITH LEVER

Splicing connector for both solid and stranded cable.

Transparent cover for easy inspection of connector. No tool needed. Solid conductors can be connected when closed.

Stripping range: 10 mm

Contact resistance: ≤0.015 Ω

Insulation resistance: ≥1000 MΩ

**Material**

Contact: Copper

Plastic parts: Polycarbonate (PC)

Spring: Stainless steel



**Product Properties:**

Transparent	Yes
With operation lever	Yes
Suitable for solid core	Yes
Suitable for flexible core	Yes

Suitable for multi-wire core	Yes
Colour	Green
Connector type	Toppklämma, öppningsbar
Packaging	Bag
Number of clamp positions	3 .
Nominal voltage	450 V
Nominal current	32 A
Operating temperature	-40-105 °C

### **Dimensions:**

Unit	pcs
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.2-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.2-4 mm <sup>2</sup>
Nominal voltage	450 V
Nominal cross section	0.2-4 mm <sup>2</sup>
AWG-range	28-12 .
MOQ	50 .

### **Approvals:**

Approved according to UKCA	Ja
Approved according to CE	Yes

### **Compliance:**

RoHS	RoHS 3 (2015/863)
Reach	No SVHC (Latest, 14 June 2023)
SCIP	Not Applicable

### **Other information:**

Trademark	NEMIQ
ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Product Group	Terminal Blocks
Alternative SKU	SC-30240

### **Logistic information:**

Barcode	733117641157
E-no	E1441277
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
Packaging	Bag
Stock code	SC-3 0240

<b>Taric code</b>	85369010
<b>Unit</b>	pcs
<b>MOQ</b>	50 .