

SanDisk Ultra® SDHC™ card and SDXC™ card from SanDisk

Made for memories you can't replace

Take better pictures and Full HD videos³ with your compact to mid-range point and shoot cameras. Available in capacities up to 256GB¹ for storing tons of photos and videos, with speeds up to 100MB/s² to quickly transfer it all to your computer.

Product Details —

Capture the moment

SanDisk Ultra SD™ cards deliver exceptional photo and video shooting performance to let you capture your memories when they happen.

Picture—and video—perfect

Capture amazing quality pictures and Full HD video³ with your compact point-and-shoot camera.

Keep shooting

Delivers up to 256GB¹ of storage so you can shoot tons of photos and hours of Full HD video (1080p)³ without changing the card.

Resistant to water, temperature fluctuations, and more

SanDisk Ultra® SD™ cards are durability tested to protect your memories from life's mishaps—waterproof, shockproof, x-ray proof, and temperature-proof⁵.

Full Specifications —

Capacity	16 GB
Compatibility	<ul style="list-style-type: none">• Compatible with SDXC and SDXC UHS-I enabled host devices.
Dimensions (L x W x H)	31.92mm x 23.91mm x 2.17mm

Product Numbers –

16 GB	SDSDUNS-016G-GN3IN
32 GB	SDSDUNR-032G-GN3IN
64 GB	SDSDUNR-064G-GN3IN
128 GB	SDSDUNR-128G-GN3IN
256 GB	SDSDUNR-256G-GN3IN

7-Year Limited Warranty

Disclosures –

1. 1GB=1,000,000,000 bytes. Actual user capacity less.
2. **(For 32GB-128GB)** Up to 100MB/s read speed; write speed lower. Based on internal testing; performance may vary depending upon host device, usage conditions, drive capacity, and other factors. 1MB=1,000,000 bytes. **(For 16GB):** Up to 80MB/s read speed; write speed lower. Based on internal testing; performance may vary depending upon host device, usage conditions, drive capacity, and other factors. 1MB=1,000,000 bytes
3. Full HD (1920x1080) video support may vary based upon host device, le attributes, and other factors.
4. USA: Product not intended for sale in the United States. If purchased in the U.S., this product is purchased as-is. No warranty, express or implied is provided in the U.S.
5. Card only.