

MSA Uncoded SFP Transceiver Module - 100BASE-BX - 100 MbE Ethernet BiDi Fiber (SMF) (SFP100BBXUST)

Product ID: SFP100BBXUST



The SFP100BBXUST is an MSA compliant upstream fiber SFP transceiver which pairs with StarTech.com's SFP100BBXDST. They are designed, programmed and tested to work with 100BASE-BX compatible MSA switches and routers. The SFP transceiver module supports a maximum distance of up to 10 km (6.2 mi) and delivers dependable 100 Mbps connectivity over fiber cabling.

Technical Specifications:

- Wavelength: 1310nmTx/1550nmRx
- Maximum Data Transfer Rate: 155 Mbps
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- Power Consumption: Less than 1 Watt
- DDM: Yes

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP Cables, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility

Applications

- Replace defective or damaged SFP modules
- Expand your network to remote segments

Features

- **MSA UNCODED SFP TRANSCEIVER:** 100Mb Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible MSA Compliant switches and routers to deliver dependable 100MbE connectivity
- **INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE:** This 100 Mb Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two.
- **TECHNICAL SPECS:** 100BASE-BX 100Mbps 100Mb Bi-Directional Upstream Single Mode (SMF) LC Connector 1310nmTx/1550nmRx Digital Diagnostic Monitoring (DDM) Distances up to 10km (6.2mi).
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself and not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24.
- **WORKS WITH MSA COMPLIANT SWITCHES:** Works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

Hardware

Warranty	Lifetime
Compatible Brand	MSA Compliant
WDM	Yes
Industry Standards	IEEE 802.3u 100BASE-BX

Performance

Maximum Data Transfer Rate	155 Mbps
Max Transfer Distance	10 km (6.2 mi)
Type	Single Mode
Wavelength	1310nmTx/1550nmRx
Fiber Operating Mode	Half/Full-Duplex
DDM	Yes



Compatible Networks 100 Mbps

Power Consumption (In Watts) < 1 W

Connector(s)

Local Unit Connectors Fiber Optic LC Duplex

Special Notes / Requirements

Note For use in 100 Mbps fiber networking equipment and media converters

Environmental

Operating Temperature 0C to 70C (32F to 158F)

Storage Temperature -40C to 85C (-40F to 185F)

Humidity 5~95% RH

Physical Characteristics

Product Length 2.4 in [60.0 mm]

Product Width 0.6 in [16.0 mm]

Product Height 0.4 in [11.0 mm]

Weight of Product 0.6 oz [18.0 g]

Packaging Information

Package Length 4.6 in [11.7 cm]

Package Width 3.6 in [92.0 mm]

Package Height 1.2 in [30.0 mm]

Shipping (Package) Weight 1.7 oz [47.0 g]

What's in the Box

Included in Package SFP transceiver

**Product appearance and specifications are subject to change without notice.*

