

# Cat 6A Extension lead



# Cat 6A Extension lead (SGPXZ\*Bk)

TUK's Category 6A low smoke zero halogen extension leads are designed manufactured and tested in accordance with the ISO and TIA standards for Category 6A. The use of an FTP cable effectively eliminates Alien Crosstalk from adjacent leads as well as protecting the lead from emissions from any other external sources. High gold plating on contacts ensures consistent high-quality mating.

# Features:

- Quick and easy extension of Category 5, 6 or 6A sockets without need for engineers
- Compliant with IEC60512-99-001 suitable for use with IEEE 802.3at (PoE+) applications
- Terminated with high gold plated RJ45 shielded plug and socket
- Fitted with flush anti-snag strain relief boots making our leads suitable for use in high density switches
- Each lead individually tested for compliance

# Specifications:

- Available as: 3m, 10m, 20m/ SGPXZ3Bk, SGPXZ10Bk, SGPXZ20Bk,
- Net weight (including primary packaging): 3m: 128g, 10m: 340g, 20m: 646g
- Dimensions: (when packed) 3m: 160x200x35mm, 10m: 190x190x50mm 20m: 190x190x50mm
- Colour: Black



Materials:

# Plug

Contacts: 50μ"/1.27μm gold plated

#### Cable:

Low Smoke Zero Halogen sheath, 4 twisted pairs of 26AWG stranded copper wires individually
mylar overfoiled

### Socket

- ABS housing over die cast nickel-plated zinc body, contacts:  $50\mu''/1.27\mu m$  gold plating over nickel, over phosphor bronze suitable for at least 500 insertions
- 4PPoE+ compliant

Packaging: Supplied in individual poly bags

Commodity code: 85177090

EAN: SGPXZ3Bk: 5055386510693 SGPXZ10Bk: 5055386510709 SGPXZ20Bk: 5055386510716

Country of Origin: China

Other lengths available to order.

See also related product - Portsaver (SGTS): https://tuk.co.uk/product/category-6a-portsaver-2/





