



DOL-1208-G05MF

SICK
Sensor Intelligence.



Illustration may differ



Ordering information

Type	Part no.
DOL-1208-G05MF	6020664

For 8-pin sensor-actuator cables, the wire colors are not standardized. Therefore, please observe the pin assignment of the sensor and the cable in the respective data sheet.

Other models and accessories → www.sick.com/

Detailed technical data


Technical specifications

Accessory group	Plug connectors and cables
Accessory family	Connecting cables
Connection type head A	Female connector, M12, 8-pin, straight
Connection type head B	Flying leads
Connection type	Flying leads
Connector material	PVC
Connector color	Black
Locking nut material	Zinc die-cast, nickel-plated
Cable	5 m, 8-wire, PVC
Jacket material	PVC
Jacket color	Black
Cable diameter	6.1 mm
Conductor cross-section	0.25 mm ²
Shielding	Shielded
Bending radius	
	Flexible use > 10 x cable diameter
Reference voltage	
	≤ 30 V
Current loading	2 A
Signal type	Sensor/actuator cable
Special feature	Special color code
Authorizations	UL
UL File No.	CYJV.E335179
Enclosure rating	IP67
Ambient operating temperature	
	Flexible use +5 °C ... +80 °C
	Stationary position -40 °C ... +80 °C
	Head -25 °C ... +90 °C

Classifications

ECI@ss 5.0	19030312
ECI@ss 5.1.4	19030312
ECI@ss 6.0	27060304
ECI@ss 6.2	27060304
ECI@ss 7.0	27060304
ECI@ss 8.0	27060304
ECI@ss 8.1	27060304
ECI@ss 9.0	27060304
ECI@ss 10.0	27060304
ECI@ss 11.0	27060304
ECI@ss 12.0	27060304
ETIM 5.0	EC000830
ETIM 6.0	EC000830
ETIM 7.0	EC003249
ETIM 8.0	EC003249
UNSPSC 16.0901	26121604

Dimensional drawing (Dimensions in mm (inch))



SICK AT A GLANCE

SICK is one of the leading manufacturers of intelligent sensors and sensor solutions for industrial applications. A unique range of products and services creates the perfect basis for controlling processes securely and efficiently, protecting individuals from accidents and preventing damage to the environment.

We have extensive experience in a wide range of industries and understand their processes and requirements. With intelligent sensors, we can deliver exactly what our customers need. In application centers in Europe, Asia and North America, system solutions are tested and optimized in accordance with customer specifications. All this makes us a reliable supplier and development partner.

Comprehensive services complete our offering: SICK LifeTime Services provide support throughout the machine life cycle and ensure safety and productivity.

For us, that is “Sensor Intelligence.”

WORLDWIDE PRESENCE:

Contacts and other locations –www.sick.com